

Shower and Eyewash Station

Frost-free

Model 39102

Norms :

CE EN 15154-1 and CE EN 15154-2
AFNOR NF X08.003.

Outdoor use.

Characteristics :

Pipes in hot galvanized steel, coated with 300/400 micron Rilsan
Color Yellow

Floor installation

Foot operated for eyewash

Foot and hand operated by platform for shower

Eyewash eyes with 2 spray heads + stainless steel filter

Shower head high flow

Water supply G1"1/4 to be connected to the drinking water system

Automatic drain valve pipes after use (Patent VPF)

Eyewash Water flow : 12l/mn

Shower water flow : 114 l/mn


Min. Pressure : 2 bars

For the safety of personnel, showers and eyewash stations are essential on sites where there is any risk of splashing of hazardous products. These units are therefore recommended for laboratories, workshops, hospitals, universities, schools, etc.

Showers and eyewash stations are first-aid equipment, which must be installed near the source of the hazard and, if possible, near a standard water supply. They must be easily accessible and clearly signposted.



Shower and Eyewash Station Frost-free Model 39102



Shower and Eyewash Station Frost-free Model 39102

SHOWER

- 100SS Shower head
- 400 Valve
- 346 Operating handle

EYEWASH

- 123 to 136 Eyewash spray head
- 150S Basin

GENERAL

- 316 Kit valve
- 131 to 134 Operating pedal
- 128 Base
- 5006 Safety signs

